

## Piezo Focus Module for M12 Lenses



Stock #19-972 **1 In Stock**

- 1 + €530<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€530,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

M12 Lens Weight: <16g **Note:**

### Physical & Mechanical Properties

Linear (Bi-directional) **Type of Movement:**

6 **Travel (mm):**

26x26x25	<b>Dimensions (mm):</b>
<5	<b>Load Capacity (g):</b>
±0.003	<b>Repeatability (mrad):</b>
1	<b>Resolution (µrad):</b>
<10	<b>Speed (mm/s):</b>

## Hardware & Interface Connectivity

Piezo Ultrasonic Linear Motor	<b>Type of Drive:</b>
Included USB A-C Adapter	<b>Power Supply:</b>

## Environmental & Durability Factors

0 to 50	<b>Operating Temperature (°C):</b>
---------	------------------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Enables Wide Focus Range for [M12 Lenses](#)
- Compact 26 x 26 x 25mm Housing
- 6mm Travel in Z-Axis

Piezo Focus Module for M12 Lenses utilize Tiny Ultrasonic Linear Actuators (TULA's) for low noise, high linearity, sub-micrometer resolution, backlash free motion. Integrated between the camera and lens, the 6mm stroke enables a wide focus range for most [M12 \(S-Mount\) lenses](#). Featuring an embedded controller, power and data communication (UART or I2C) interface via 5-pin flat cable or micro USB connection (USB cable included). Piezo Focus Module for M12 Lenses are ideal for lightweight OEM systems and systems in special environments such as strong EMI fields. These modules feature a standard mounting socket with a 22mm hole spacing and can be mounted to board level cameras using M1.4 x 3.5mm screws.

**Note:** Custom sockets may be required to integrate with board level cameras.