

Piezo Focus Module for M12 Lenses



Stock #19-972 2 In Stock

-

1

+

 €530⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€530,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
M12 Lens Weight: <16g	Note:
Physical & Mechanical Properties	
Linear (Bi-directional)	Type of Movement:
6	Travel (mm):

26x26x25	Dimensions (mm):
<5	Load Capacity (g):
±0.003	Repeatability (mrad):
1	Resolution (μrad):

<10	Speed (mm/s):
-----	---------------

Hardware & Interface Connectivity

Piezo Ultrasonic Linear Motor	Type of Drive:
Included USB A-C Adapter	Power Supply:

Environmental & Durability Factors

0 to 50	Operating Temperature (°C):
---------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Enables Wide Focus Range for [M12 Lenses](#)
- Compact 26 x 26 x 25mm Housing
- 6mm Travel in Z-Axis

Piezo Focus Module for M12 Lenses utilize Tiny Ultrasonic Linear Actuators (TULA's) for low noise, high linearity, sub-micrometer resolution, backlash free motion. Integrated between the camera and lens, the 6mm stroke enables a wide focus range for most [M12 \(S-Mount\) lenses](#). Featuring an embedded controller, power and data communication (UART or I2C) interface via 5-pin flat cable or micro USB connection (USB cable included). Piezo Focus Module for M12 Lenses are ideal for lightweight OEM systems and systems in special environments such as strong EMI fields. These modules feature a standard mounting socket with a 22mm hole spacing and can be mounted to board level cameras using M1.4 x 3.5mm screws.

Note: Custom sockets may be required to integrate with board level cameras.