

[See all 71 Products in Family](#)

PLC (Programmable Logic Controller) I/O Cable Hirose 6 Pin 10m

See More by [Basler](#)



PLC (Programmable Logic Controller) I/O Cable Hirose 6 Pin 10m, #68-467



Stock **#68-467** 4 In Stock

-

1

+

€118⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€118,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Camera Accessory

Type:

Regulatory Compliance

Compliant

RoHS 2015:


View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Perfect Analog Replacement
- Ultra-Small Form Factor
- Power Over Ethernet (PoE)
- Includes Basler Pylon Driver

Basler ace GigE Cameras are economical Gigabit Ethernet cameras that provide an ideal upgrade opportunity for analog camera users. With a small form factor matching that of many analog cameras (29 x 29mm), the ace can be a drop-in replacement to an existing analog system or a great choice to start a new project. Basler ace GigE Cameras can use Power Over Ethernet (PoE) (2 GigE cables required). The cameras can have long cable lengths and are the optimal choice for use on a factory floor. All cameras include the industry-proven Basler Pylon SDK Software and Driver.

Technical Information



MT9P031 Sensor QE Curve