

[See all 7 Products in Family](#)

Visible-NIR Reflection/Backscatter Probe, Silicone-coated steel monocoil

See More by [Ocean Optics](#)



Stock #90-562 **NEW** 1 In Stock

⊖ 1 ⊕ €1.160⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€1.160,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

QR400-7-VIS-NIR **Model Number:**

Visible-NIR Reflection/Backscatter Probe, Silicone-coated steel monocoil **Title:**

Physical & Mechanical Properties

400 **Core Diameter (µm):**

Jacket Material:
Silicone Monocoil, PVDF Zip Tube

Long Term Bend Radius (cm):
16

Short Term Bend Radius (cm):
8

Optical Properties

Wavelength Range (nm):
400 - 2100

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Versatile Sampling for Diffuse/Specular Reflectance, Backscatter & Fluorescence
- Various Wavelength and Environmental Durability Models
- Extreme Solarization-Resistant (XSR) Probe Features Ultra-Low Loss Fiber for Harsh UV Exposure
- Connects Directly with Ocean Optics Spectrometers & Accessories

Ocean Optics Reflection/Backscatter Probes are compact, fiber-coupled sampling tools for measuring diffuse and specular reflectance, backscatter, or fluorescence in solids, solutions, or powders, and connect directly with [Ocean Optics Spectrometers and Accessories](#). They provide quantitative insights into a sample's color, appearance, and chemical composition. Choose from Visible-NIR, Solarization-Resistant, or XSR models for applications ranging from routine reflectance to demanding UV measurements. With durable jacketing, precision ferrules, and solarization-resistant fiber, the rugged design ensures reliable performance even in harsh conditions. Ocean Optics Reflection/Backscatter Probes can be optimized for UV applications, with the XSR probe featuring ultra-low loss fiber designed to withstand harsh UV exposure.