

## Spatial Filter Movement



Stock #39-976 **5 In Stock**

- 1 + €660<sup>.00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€660,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

Pinhole: ±3 in X-Axis and Y-Axis  
Objective: 19 in Z-Axis **Travel (mm):**

9.5 **Aperture (mm):**

2.5 in Z-Axis **Accuracy (µm):**

## Threading & Mounting

**Mount:**  
36 TPI 55° Whitworth (DIN Objective)

**Mounting Threads:**  
1/4-20

---

**Leadscrew Thread:**  
50.8 TPI in X-Axis and Y-Axis

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)


## Product Details

- X-Y Adjustable
- Pre-Mounted on a Gimbal Tilt-Table
- Open-Style Design

Our precision open-style spatial filter mechanism features a ball bearing, spring-loaded dual stainless rail objective movement with a micrometer drive. The pinhole mount accepts standard 3/8" (9.5mm) discs from our line of [Pinholes & Slits](#) and is X-Y adjustable via two fine thumbscrews. This entire assembly is mounted on a gimbal tilt-table with X-Y two-axis adjustment by two fine thumbscrews. A 1/4-20 tap hole on the gimbal platform base allows for easy mounting to posts or other positioning equipment. The [Understanding Spatial Filters](#) application note will help you select the appropriate components for your laser application.

**Note:** Spatial Filter does not operate with 5.5mm objective. Spatial Filter Movement is only compatible with the following objectives: DIN Achromatic 4X ([#43-902](#)), DIN Plan 4X ([#67-706](#)), and the JIS Achromatic 10X

## Technical Information



Input Beam Diameter (mm)	Magnification/Focal Length of Objective Lens (mm)	
	4X/31.04	10X/17.13
0.96	35µm	20µm
0.81	50µm	25µm
0.75	50µm	25µm
0.70	50µm	25µm
0.68	50µm	25µm
0.63	50µm	35µm
0.48	50µm	35µm