

[See all 3 Products in Family](#)

UV Radiometer Unit



UV Radiometer Unit, #88-136

Stock **#88-136** **1 In Stock**

⊖ 1 ⊕ €1.160⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.160,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

3.5 digit LCD **Type of Display:**
2.8 readings/sec **Conversion Rate:**

Physical & Mechanical Properties

0.3 **Weight (kg):**

157 x 51 x 91 **Dimensions (mm):**

± 2 **Accuracy (%):**

Electrical

Intensity Range:
Switchable:
0 – 20 mW/cm₂
0 – 200 μW/cm₂
0 – 2000 μW/cm₂

Hardware & Interface Connectivity

9 V Battery (not included) **Power Requirement:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer's range switch allows the selection of three intensity ranges.

Note: The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.