

[See all 12 Products in Family](#)

# VIS-NIR Fiber Patch Cord, 200 µm Core, Silicone-coated steel monocoil

See More by [Ocean Optics](#)



Stock #90-548 NEW **1 In Stock**

⊖ 1 ⊕ €272<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	€272,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

QP200-2-VIS-NIR **Model Number:**

#### Physical & Mechanical Properties

2 **Length (m):**

200 **Core Diameter (µm):**

**Jacket Material:**

Silicone-coated steel monocoil

## Optical Properties

0.22 **Numerical Aperture NA:**

400 - 2100 **Wavelength Range (nm):**

## Hardware & Interface Connectivity

SMA **Connector:**

## Material Properties

Polyimide **Buffer Material:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

## Product Details

- Connects Directly with Ocean Optics Spectrometers & Accessories
- Broad Wavelength Coverage: VIS-NIR, SR, and XSR Fibers Optimized for 180–2100 nm
- Solarization-Resistant Fibers Maintain Signal Accuracy Under Harsh UV
- Multiple Jacketing Choices for Durability and Tight Bend Radius Needs

Ocean Optics offers a complete line of premium optical fiber patch cords compatible with [Ocean Optics spectrometers](#) to suit a range of VIS-NIR and UV-NIR spectroscopy needs. Use them as illumination or read fibers to connect spectrometers, light sources, probes, or sampling accessories with maximum transmission efficiency and minimal signal loss. Choose standard visible-NIR assemblies for broadband applications or select solarization-resistant options to maintain signal fidelity when working with high UV power. Ocean Optics Spectrometer Patch Cords are available with a range of jacketing options designed to enhance durability and accommodate applications requiring a tight bend radius.

**VIS-NIR Patch Cords (400–2100 nm):** Best for routine broadband spectroscopy with minimal OH content, minimizing light absorption caused by hydroxyl ions (OH<sup>-</sup>), for efficient NIR transmission.

**Solarization-Resistant Patch Cords (200–1100 nm):** Ideal for UV-NIR work where standard silica fibers degrade under high UV exposure.

**Extreme Solarization-Resistant Patch Cords (180–800 nm):** Essential for deep-UV applications where the highest UV resistance is required.